

LINEA CLINIC

5944UAP100R36-32S30

EAN 4031582444926



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ● ● |
| Movement noise | ● ● ● ● ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ● ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|---|
| Product name | Linea clinic |
| Housing type | Swivel castor with central, total or directional lock |
| Standard | EN12530 - Devices Castors |
| Load capacity at 1.8 mph | 264.55 lb |
| Load capacity Static | 529.11 lb |
| Temperature range (Minimum) | 14 °F |
| Temperature range (Maximum) | 104 °F |
| Overall height | 4.65 in |
| Overall width | 3.23 in |
| Certification | Tested and monitored by TÜV Süd |

WHEEL

| | |
|-----------------------|------------------------|
| Body material | Polyamide |
| Tread material | Polyurethane, injected |
| Bearing | Precision ball bearing |
| Threadguards | With threadguard |
| Diameter | 3.94 in |
| Tread width | 0.79 in |
| Hardness of tread (A) | 92 Shore A |

HOUSING

| | |
|---------------------|------------------------|
| Material | Polyamide |
| Fork shape | Twin wheel housing |
| Swivel bearing | Precision ball bearing |
| Offset | 1.26 in |
| Swivel radius | 3.54 in |
| Swivel interference | 7.09 in |
| Dome diameter | 2.05 in |

FITTING

| | |
|------------------------------|--|
| Fitting type | Stem with cam hole for profile bars, short version |
| Bolt diameter | 1.26 in |
| Bolt length | 2.01 in |
| Bolt mounting holes quantity | 4 |



LINEA CLINIC

5944UAP100R36-32S30

EAN 4031582444926



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

