

# ELASTECH

UFC100X34@08X45

EAN 4031582422269



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polyamide
Tread material	Elastic tire, non-marking, vulcanized
Bearing	Precision ball bearing, stainless
Threadguards	With threadguard
Diameter	100 mm
Tread width	34 mm
Axle hole diameter	8 mm
Hub length	45 mm
Hardness of tread (A)	64 Shore A

## HOUSING

Stainless	✓
-----------	---

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Elastech
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	160 kg
Load capacity Static	320 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	80 °C
Overall weight	0.302 kg

# ELASTECH

UFC100X34@08X45

EAN 4031582422269



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

