PRODUCT INFORMATION

# AGILA CARE

## 2476XSP150R36-32S30 D 4xM6

EAN 4031582358209



Image may differ from the original product

### PERFORMANCE

| | |
|---|---|
| Roll Performance | ● ● ● ○ ○ |
| Movement Noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion Resistance | ● ● ● ○ ○ |

### CORE ATTRIBUTES

| | |
|---|---|
| Product Name | Agila care |
| Type | Swivel castor with central, total lock |
| Standard | EN12530 - Devices Castors |
| Load capacity at 3 km/h | 100 kg |
| Electric Conductive | Yes |
| Stainless | No |
| Load capacity Static | 200 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 60 °C |
| Overall Height | 188 mm |
| Overall width | 60 mm |
| Overall weight | 1.11 kg |

### HOUSING

| | |
|---|---|
| Housing Material | Steel sheet, medium |
| Fork shape | Broad |
| Swivel Bearing | Two ball races |
| Housing Color | Blue passivated |
| Offset | 45 mm |
| Swivel radius | 120 mm |
| Swivel interference | 240 mm |
| Dome diameter | 60 mm |

### WHEEL

| | |
|---|---|
| Body material | Polyamide, electric conductive |
| Tread Material Mix | Polyurethane, injected, electric-conductive |
| Bearing | Precision ball bearing |
| Wheel Color | Silver grey (RAL7001) |
| Threadguards | With threadguard |
| Diameter | 150 mm |
| Tread width | 32 mm |
| Body width | 32 mm |
| Hardness of tread (A) | 91 Shore A |
| Hardness of tread (D) | 40 Shore D |

### FITTING

| | |
|---|---|
| Brake cam | hex cam |
| Fitting type | Stem with cam hole for profile bars, short version |
| Bolt diameter | 32 mm |
| Bolt length | 51 mm |
| Bolt thread position | 7 mm |
| Bolt mounting holes quantity | 4 |

© Copyright 2026 TENTE International GmbH


# AGILA CARE

## 2476XSP150R36-32S30 D 4xM6

EAN 4031582358209

Order number 00063721

**Product Drawings**



© Copyright 2026 TENTE International GmbH