

MAXTECH

UAK 050X20-Ø6,1

EAN 4031582322835
Order number 00008698



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Cone ball bearing
Wheel color	Silver grey (RAL7001)
Threadguards	With threadguard
Diameter	50 mm
Tread width	20 mm
Axle hole diameter	6 mm
Hub length	22 mm
Body width	20 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Maxtech
Type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	50 kg
Load capacity Static	100 kg
Temperature range (Minimum)	-25 °C
Temperature range (Maximum)	80 °C
Overall weight	0.066 kg

MAXTECH

UAK 050X20-Ø6,1

EAN 4031582322835
Order number 00008698



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

