

DURATECH SILENT

UOT 125x40-Ø8,4 HL45

EAN 4031582338058



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Precision ball bearing, damped
Wheel color	Natural white
Diameter	4.92 in
Tread width	1.57 in
Axle hole diameter	0.33 in
Hub length	1.77 in
Body width	1.57 in
Hardness of tread (D)	75 Shore D

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Duratech silent
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	661.39 lb
Electric conductive	no
Stainless	no
Load capacity Static	1322.77 lb
Temperature range (Minimum)	-22 °F
Temperature range (Maximum)	176 °F
Overall weight	0.84 lb

DURATECH SILENT

UOT 125x40-Ø8,4 HL45

EAN 4031582338058

Order number 00033628
Product Drawings



BETTER MOBILITY. BETTER LIFE.

