

ZETA STAINLESS

8670TOO160P63

EAN 4031582313444



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Zeta stainless
Type	Swivel caster
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	1763.7 lb
Load capacity at 3.7 mph	1410.96 lb
Electric conductive	no
Stainless	Yes
Load capacity Static	3527.39 lb
Temperature range (Minimum)	-22 °F
Temperature range (Maximum)	176 °F
Overall height	7.87 in
Overall width	3.78 in
Overall weight	6.26 lb

HOUSING

Housing Material	Stainless steel, heavy
Fork shape	Broad, reinforced
Swivel bearing	Two ball races
Housing Color	Stainless steel
Offset	2.17 in
Swivel radius	5.31 in
Swivel interference	10.63 in
Dome diameter	3.78 in

WHEEL

Body material	Polyamide, heavy
Tread material	Identical with wheel body
Bearing	Plain bearing
Axle	Screwed with nut
Wheel color	Natural white
Threadguards	Without threadguard
Diameter	6.3 in
Tread width	1.97 in
Body width	1.97 in
Hardness of tread (D)	75 Shore D

FITTING

Fitting type	Rectangular plate
Plate length	5.39 in
Plate width	4.13 in
Plate hole length (Minimum)	2.91 in
Plate hole length (Maximum)	3.15 in
Plate hole width (Minimum)	2.91 in
Plate hole width (Maximum)	4.13 in
Plate hole diameter	0.43 in

ZETA STAINLESS

8670TOO160P63

EAN 4031582313444

Order number 00830093

Product Drawings



BETTER MOBILITY. BETTER LIFE.

