

# NOVATECH

FTP200x80-Ø25 HL92

EAN 4031582419061



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

### WHEEL


|                       |                        |
|-----------------------|------------------------|
| Body material         | Cast iron              |
| Tread Material Mix    | Polyurethane, casted   |
| Bearing               | Precision ball bearing |
| Threadguards          | With threadguard       |
| Diameter              | 200 mm                 |
| Tread width           | 80 mm                  |
| Axle Hole Diameter    | 25 mm                  |
| Hub Length            | 92 mm                  |
| Hardness of tread (A) | 92 Shore A             |

### PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ● ○ |
| Movement Noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion Resistance | ● ● ● ○ ○ |

### CORE ATTRIBUTES

|                             |                              |
|-----------------------------|------------------------------|
| Product Name                | Novatech                     |
| Type                        | Wheel                        |
| Standard                    | EN12533 - Heavy Duty Castors |
| Load capacity at 4 km/h     | 1680 kg                      |
| Load capacity at 6 km/h     | 1400 kg                      |
| Electric Conductive         | No                           |
| Stainless                   | No                           |
| Load capacity Static        | 3360 kg                      |
| Temperature range (Minimum) | -20 °C                       |
| Temperature range (Maximum) | 60 °C                        |
| Overall weight              | 7.06 kg                      |




PRODUCT INFORMATION

**NOVATECH**

FTP200x80-Ø25 HL92

EAN 4031582419061



BETTER MOBILITY. BETTER LIFE.