

PRODUCT INFORMATION

SUPRATECH

PHP125x32-Ø8.3, antistatique

EAN 4031582489088



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Supratech
Type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	100 kg
Electric Conductive	No
Stainless	No
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.29 kg

WHEEL

Body material	Polypropylene
Tread Material Mix	Thermoplastic rubber, antistatic
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	125 mm
Tread width	32 mm
Axle Hole Diameter	8.3 mm
Hub Length	36.5 mm
Hardness of tread (A)	87 Shore A

SUPRATECH

PHP125x32-Ø8.3, antistatique

EAN 4031582489088



BETTER MOBILITY. BETTER LIFE.

Product Drawings

