

# NOVATECH

ITP100X40-Ø12 HL26 FLAT

EAN 4031582487916



Image may differ from the original product

## WHEEL

Body material	Aluminium
Tread profile	flat
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Threadguards	Without threadguard
Diameter	100 mm
Tread width	40 mm
Axle hole diameter	12 mm
Hub length	26 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Novatech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	300 kg
Load capacity at 6 km/h	240 kg
Load capacity Static	600 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.334 kg

# NOVATECH

ITP100X40-Ø12 HL26 FLAT

EAN 4031582487916



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

