

ALPHA

3470PVO160P30-13

EAN 4031582304145



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ● ● ●
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Alpha
Housing type	Swivel castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	135 kg
Load capacity Static	270 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	195 mm
Overall weight	1.878 kg

WHEEL

Body material	Polypropylene
Tread material	Solid rubber, black
Bearing	Plain bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	160 mm
Tread width	40 mm
Hardness of tread (A)	85 Shore A

HOUSING

Material fork	Steel sheet, heavy
Fork shape	Broad
Swivel bearing	Two ball races
Offset	55 mm
Swivel radius	135 mm
Swivel interference	270 mm

FITTING

Fitting type	Bolt hole
Bolt hole diameter	13 mm

ALPHA

3470PVO160P30-13

EAN 4031582304145



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

