

# ALPHA

3478UOJ108P62 T/G-SMALL

EAN 4031582396812  
Order number 00002499



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Alpha
Housing type	Fixed castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	200 kg
Load capacity Static	400 kg
Temperature range (Minimum)	-25 °C
Temperature range (Maximum)	80 °C
Overall height	132 mm
Overall width	85 mm
Overall weight	0.438 kg

## WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Roller bearing
Axle	Screwed with nut
Wheel color	Natural white
Threadguards	With threadguard
Diameter	108 mm
Tread width	36 mm
Body width	36 mm
Hardness of tread (D)	75 Shore D

## HOUSING

Material fork	Steel sheet, heavy
Fork shape	Broad
Colour	Blue passivated

## FITTING

Fitting type	Rectangular plate
Plate length	103 mm
Plate width	85 mm
Plate hole length (Minimum)	77 mm
Plate hole length (Maximum)	60 mm
Plate hole width (Minimum)	77 mm
Plate hole width (Maximum)	80 mm
Plate hole diameter	9 mm

# ALPHA

3478UOJ108P62 T/G-SMALL

EAN 4031582396812  
Order number 00002499



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

