PRODUCT INFORMATION

MAXTECH

UAR 125x38-Ø12 HL44 natural/3004

EAN 4031582323177



Image may differ from the original product

WHEEL

Body material	Polyamide
Tread Material Mix	Polyurethane, injected
Bearing	Roller bearing
Wheel Color	Natural white
Threadguards	Without threadguard
Diameter	125 mm
Tread width	38 mm
Axle Hole Diameter	12 mm
Hub Length	44 mm
Body width	38 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

PERFORMANCE

Roll Performance	●●●○○
Movement Noise	●●●○○
Attrition	●●●●○
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Maxtech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	300 kg
Electric Conductive	No
Stainless	No
Load capacity Static	600 kg
Temperature range (Minimum)	-25 °C
Temperature range (Maximum)	80 °C
Overall weight	0.32 kg

© Copyright 2026 TENTE International GmbH


MAXTECH

UAR 125x38-Ø12 HL44 natural/3004

EAN 4031582323177

Order number 00034120

Product Drawings



© Copyright 2026 TENTE International GmbH