

# AGILA TWIN

2970PJ050P40 (12)

EAN 4031582255317



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                           |
|-----------------------------|---------------------------|
| Product name                | Agila twin                |
| Housing type                | Swivel castor             |
| Standard                    | EN12530 - Devices Castors |
| Load capacity at 3 km/h     | 70 kg                     |
| Load capacity Static        | 140 kg                    |
| Temperature range (Minimum) | -20 °C                    |
| Temperature range (Maximum) | 60 °C                     |
| Overall height              | 69 mm                     |
| Overall weight              | 0.221 kg                  |

## WHEEL

|                       |                                |
|-----------------------|--------------------------------|
| Body material         | Polypropylene                  |
| Tread material        | Thermoplastic rubber           |
| Bearing               | Plain bearing with spacer tube |
| Threadguards          | Without threadguard            |
| Diameter              | 50 mm                          |
| Tread width           | 19 mm                          |
| Hardness of tread (A) | 87 Shore A                     |

## HOUSING

|                     |                     |
|---------------------|---------------------|
| Material fork       | Steel sheet, medium |
| Fork shape          | Twin wheel housing  |
| Swivel bearing      | Two ball races      |
| Offset              | 25 mm               |
| Swivel radius       | 53 mm               |
| Swivel interference | 106 mm              |

## FITTING

|                             |              |
|-----------------------------|--------------|
| Fitting type                | Square plate |
| Plate length                | 60 mm        |
| Plate width                 | 60 mm        |
| Plate hole length (Minimum) | 38 mm        |
| Plate hole length (Maximum) | 48 mm        |
| Plate hole width (Minimum)  | 38 mm        |
| Plate hole width (Maximum)  | 48 mm        |
| Plate hole diameter         | 6.3 mm       |

# AGILA TWIN

2970PJ1050P40 (12)

EAN 4031582255317



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

