

NOVATECH

RK.ETP082X96-Ø52X14

EAN 4031582330656



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Undefined
Tread material	Polypropylene, soft
Diameter	3.23 in
Tread width	3.78 in
Hardness of tread (A)	92 Shore A
Ball bearing diameter	2.05 in
Ball bearing width	0.55 in

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Type	Wheel
Load capacity at 1.8 mph	1653.47 lb
Load capacity Static	3306.93 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F

TECHNICAL DRAWINGS

