PRODUCT INFORMATION

NOVATECH

ITP 100x40-Ø12 HL26



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●●○
Movement Noise	●●●○○
Attrition	●●●●○
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Novatech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	300 kg
Load capacity at 6 km/h	240 kg
Electric Conductive	No
Stainless	No
Load capacity Static	600 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall weight	0.43 kg

WHEEL

Tread profile	flat
Body material	Aluminium
Tread Material Mix	PUR casted premium
Bearing	Precision ball bearing
Wheel Color	Honey yellow (RAL1005)
Threadguards	Without threadguard
Diameter	100 mm
Tread width	40 mm
Axle Hole Diameter	12 mm
Hub Length	26 mm
Body width	40 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D


© Copyright 2026 TENTE International GmbH

NOVATECH

ITP 100x40-Ø12 HL26

BETTER MOBILITY. BETTER LIFE.


Product Drawings



© Copyright 2026 TENTE International GmbH

NOVATECH

ITP 100x40-DTZ HL26



© Copyright 2026 TENTE International GmbH