

# DURATECH

U00125X43-Ø12 HL 58

EAN 4031582419023



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## TOCAK

|                            |                          |
|----------------------------|--------------------------|
| Materijal za telo          | poliamid                 |
| materijal omotaca          | Identično sa telom Tocak |
| Nošenje                    | klizni lezaj             |
| stitnici omotaca           | Bez stražara             |
| Prečnik                    | 125 mm                   |
| Širina omotac              | 43 mm                    |
| dimenzija rupa osovine     | 20 mm                    |
| dužina glavnice            | 58 mm                    |
| Teškoća gazećeg omotac (D) | 75 Šor D                 |

## PERFORMANSE

|                        |           |
|------------------------|-----------|
| Performanse kotrljanja | ● ● ● ○ ○ |
| Buka u pokretu         | ● ● ● ○ ○ |
| Ishrana                | ● ● ● ● ● |
| otpornost na rdju      | ● ● ● ○ ○ |

## OSNOVNI ATRIBUTI

|                                |                              |
|--------------------------------|------------------------------|
| Naziv proizvoda                | Duratech                     |
| Tip kućišta                    | Tocak                        |
| Standard                       | EN12532 - transportna oprema |
| Nosivost na 4 km/h             | 300 kg                       |
| Statički Nosivost              | 600 kg                       |
| Temperaturni opseg (Minimalno) | -40 °C                       |
| Opseg temperature (maksimalni) | 80 °C                        |
| Ukupna težina                  | 0,244 kg                     |

# DURATECH

U00125X43-Ø12 HL 58

EAN 4031582419023



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

---

