

# GLIDE

A229POI050B10-11x20

EAN 4031582319606



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                     |
|-----------------------------|---------------------|
| Product name                | Glide               |
| Type                        | Customized solution |
| Load capacity at 1.8 mph    | 66.14 lb            |
| Electric conductive         | no                  |
| Stainless                   | no                  |
| Temperature range (Minimum) | -4 °F               |
| Temperature range (Maximum) | 140 °F              |
| Overall height              | 1.3 in              |
| Overall width               | 1.97 in             |
| Overall weight              | 0.12 lb             |

## HOUSING

|                  |                 |
|------------------|-----------------|
| Housing Material | Polypropylene   |
| Fork shape       | Straight        |
| Swivel bearing   | Stem, swiveling |
| Dome diameter    | 1.5 in          |
| Collar diameter  | 1.97 in         |

## WHEEL

|                       |                                |
|-----------------------|--------------------------------|
| Body material         | Polypropylene                  |
| Tread material        | Identical with wheel body      |
| Bearing               | Plain bearing with spacer tube |
| Threadguards          | Without threadguard            |
| Diameter              | 1.97 in                        |
| Hardness of tread (D) | 65 Shore D                     |

## FITTING

|               |                                  |
|---------------|----------------------------------|
| Fitting type  | Stem with grip ring, with collar |
| Stem diameter | 0.43 in                          |

# GLIDE

A229POI050B10-11x20

EAN 4031582319606

Order number 00072176

**Product Drawings**



BETTER MOBILITY. BETTER LIFE.

