

LEVINA LIGHT

5220PJP075P52

EAN 4031582492538



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Levina light
Housing type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	75 kg
Load capacity Static	150 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall height	116 mm
Overall weight	0.384 kg

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	75 mm
Tread width	25 mm
Hardness of tread (A)	87 Shore A

HOUSING

Material fork	Polyamide
Fork shape	Straight
Swivel bearing	Stem, swiveling
Offset	27 mm
Swivel radius	64.5 mm
Swivel interference	129 mm

FITTING

Fitting type	Rectangular plate, US-bolt hole spacing
Plate length	95 mm
Plate width	70 mm
Plate hole length (Minimum)	44.5 mm
Plate hole length (Maximum)	52 mm
Plate hole width (Minimum)	72 mm
Plate hole width (Maximum)	76 mm
Plate hole diameter	11 mm

LEVINA LIGHT

5220PJP075P52

EAN 4031582492538



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

