

DURATECH

TOP 082X80-Ø20 HL82

EAN 4031582322606

Broj porudžbine 00802945



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	poliamid težak
materijal omotaca	Identično sa telom Tocak
Nošenje	precizini kuglicni lezaj
Boja Tocak	Prirodno belo
stitnici omotaca	Bez stražara
Prečnik	82 mm
Širina omotac	80 mm
dimenzija rupa osovina	20 mm
dužina glavcine	82 mm
Širina tela	80 mm
Teškoća gazećeg omotac (D)	75 Šor D
Tip ležaja	6204ZV

PERFORMANSE

Performanse kotrljanja	● ● ● ● ●
Buka u pokretu	● ● ○ ○ ○
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Duratech
Tip	Tocak
Standard	EN12533 - Tockoviza teske terete
Nosivost na 4 km/h	750 kg
Nosivost na 6 km/h	600 kg
Statički Nosivost	1500 kg
Temperaturni opseg (Minimalno)	-40 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	0,506 kg

DURATECH

TOP 082X80-Ø20 HL82

EAN 4031582322606

Broj porudžbine 00802945



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

