

## S70-10X25 / 10 BRASS

EAN 4031582445657



Image may differ from the original product

### PERFORMANCE

Corrosion resistance ● ● ● ○ ○

### CORE ATTRIBUTES

Product name	Accessory
Housing type	Accessory
Load capacity at 3 km/h	40 kg
Load capacity Static	80 kg
Overall height	6 mm
Overall weight	0.03 kg

### FITTING

Fitting type	Threaded stem with hexagon neck, top
Stem length	25 mm

S70-10X25 / 10 BRASS

EAN 4031582445657



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

