

DELTA CENTRAL

3645ITP160P67 OH225 SOFT CV

EAN 4031582366501
Order number 00835383



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Delta central
Type	Swivel castor with wheel brake
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	1212.54 lb
Load capacity at 3.7 mph	970.03 lb
Load capacity Static	2425.08 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	140 °F
Overall height	8.86 in
Overall width	3.7 in
Overall weight	8.58 lb

WHEEL

Body material	Aluminum
	soft
	convex
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Wheel color	Traffic gray A (RAL7042)
Threadguards	Without threadguard
Diameter	6.3 in
Tread width	1.97 in
Body width	1.97 in
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

HOUSING

Material	Steel sheet, heavy
Fork shape	Broad, reinforced
Swivel bearing	Precision ball bearing
Color	Blue passivated
Offset	2.17 in
Swivel radius	5.31 in
Swivel interference	10.63 in
Dome diameter	3.7 in

FITTING

Fitting type	Plate with central locking
Plate length	5.59 in
Plate width	4.33 in
Plate hole length (Maximum)	3.05 in
Plate hole width (Maximum)	4.13 in
Plate hole diameter	0.51 in

DELTA CENTRAL

3645ITP160P67 OH225 SOFT CV

EAN 4031582366501
Order number 00835383



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

