

# LUMINA

6A20YGI050L51-10 ZAMAK/9011/9011

EAN 4031582335804



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ● ○ |
| Movement Noise       | ● ● ● ● ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion Resistance | ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                             |
|-----------------------------|-----------------------------|
| Product Name                | Lumina                      |
| Type                        | Swivel castor               |
| Standard                    | EN12528 - Furniture Castors |
| Load capacity at 3 km/h     | 40 kg                       |
| Electric Conductive         | Yes                         |
| Stainless                   | No                          |
| Load capacity Static        | 80 kg                       |
| Temperature range (Minimum) | -20 °C                      |
| Temperature range (Maximum) | 60 °C                       |
| Overall Height              | 56 mm                       |
| Overall width               | 55 mm                       |
| Overall weight              | 0.12 kg                     |

## HOUSING

|                     |                              |
|---------------------|------------------------------|
| Housing Material    | Zinc-die-casting / Aluminium |
| Fork shape          | Twin wheel housing, closed   |
| Swivel Bearing      | Stem, swiveling              |
| Housing Color       | Chrome                       |
| Offset              | 20 mm                        |
| Swivel radius       | 54 mm                        |
| Swivel interference | 108 mm                       |
| Dome diameter       | 0 mm                         |

## WHEEL

|                       |                                           |
|-----------------------|-------------------------------------------|
| Body material         | Polypropylene, electric conductive        |
| Tread Material Mix    | Thermoplastic rubber, electric-conductive |
| Bearing               | Plain bearing with spacer tube            |
| Axle                  | Riveted                                   |
| Tread Color           | Graphite black (RAL9011)                  |
| Wheel Color           | Graphite black (RAL9011)                  |
| Threadguards          | Without threadguard                       |
| Diameter              | 50 mm                                     |
| Tread width           | 10 mm                                     |
| Axle Hole Diameter    | 0 mm                                      |
| Hub Length            | 0 mm                                      |
| Body width            | 10 mm                                     |
| Hardness of tread (A) | 87 Shore A                                |

## FITTING

|                    |                    |
|--------------------|--------------------|
| Fitting type       | Blind hole for B10 |
| Bolt hole diameter | 10 mm              |

# LUMINA

6A20YGI050L51-10 ZAMAK/9011/9011

EAN 4031582335804

Order number 00079236

**Product Drawings**



BETTER MOBILITY. BETTER LIFE.

