

DURATECH HEAT

BOG080x35-Ø12

EAN 4031582436730



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Plastic thermoset, heat-resistant
Tread Material Mix	Identical with wheel body
Bearing	Dry bearing bush
Diameter	80 mm
Tread width	35 mm
Axle Hole Diameter	12 mm
Hub Length	43.5 mm
Hardness of tread (D)	85 Shore D

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion Resistance	● ● ● ● ●

CORE ATTRIBUTES

Product Name	Duratech heat
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	100 kg
Electric Conductive	No
Stainless	No
Load capacity Static	200 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	280 °C
Overall weight	0.18 kg