

PRODUCT INFORMATION

DURATECH HEAT

BOG080x35-Ø12

EAN 4031582436730



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

|                       |                                   |
|-----------------------|-----------------------------------|
| Body material         | Plastic thermoset, heat-resistant |
| Tread Material Mix    | Identical with wheel body         |
| Bearing               | Dry bearing bush                  |
| Diameter              | 80 mm                             |
| Tread width           | 35 mm                             |
| Axle Hole Diameter    | 12 mm                             |
| Hub Length            | 43.5 mm                           |
| Hardness of tread (D) | 85 Shore D                        |

PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ○ ○ |
| Movement Noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ● |
| Corrosion Resistance | ● ● ● ● ● |

CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product Name                | Duratech heat                 |
| Type                        | Wheel                         |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 4 km/h     | 100 kg                        |
| Electric Conductive         | No                            |
| Stainless                   | No                            |
| Load capacity Static        | 200 kg                        |
| Temperature range (Minimum) | -40 °C                        |
| Temperature range (Maximum) | 280 °C                        |
| Overall weight              | 0.18 kg                       |