PRODUCT INFORMATION

BASETECH

POI 038x20-Ø6,1 HL21,5

EAN 4031582320695



Image may differ from the original product

WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Wheel color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	1.5 in
Tread width	0.79 in
Axle hole diameter	0.24 in
Hub length	0.85 in
Body width	0.79 in
Hardness of tread (D)	65 Shore D

PERFORMANCE

Roll Performance	●●●○○
Movement noise	●●●○○
Attrition	●●●○○
Corrosion resistance	●●●○○

CORE ATTRIBUTES

Product name	Basetech
Type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	77.16 lb
Electric conductive	no
Stainless	no
Load capacity Static	154.32 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	0.02 lb

© Copyright 2026 TENTE International GmbH


BASETECH

POI 038x20-Ø6,1 HL21,5

EAN 4031582320695

Order number 00050767

Product Drawings



© Copyright 2026 TENTE International GmbH