

MAXTECH

UAD100X30-Ø12 HL44,4 BURDEOS

EAN 4031582452839



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Roller bearing, stainless
Diameter	100 mm
Tread width	30 mm
Axle hole diameter	12 mm
Hub length	44.4 mm
Hardness of tread (D)	42 Shore D

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Maxtech
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	150 kg
Load capacity Static	300 kg
Temperature range (Minimum)	-25 °C
Temperature range (Maximum)	80 °C
Overall weight	0.227 kg

MAXTECH

UAD100X30-Ø12 HL44,4 BURDEOS

EAN 4031582452839



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

