

PRODUCT INFORMATION

DURATECH HEAT

BOG080x35-Ø8 HL45,5 (casquillo zinc)

EAN 4031582416459



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Duratech heat
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	220.46 lb
Electric conductive	no
Stainless	no
Load capacity Static	440.92 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	536 °F
Overall weight	0.46 lb

WHEEL

Body material	Plastic thermoset, heat-resistant
Tread material	Identical with wheel body
Bearing	Dry bearing bush
Diameter	3.15 in
Tread width	1.38 in
Axle hole diameter	0.31 in
Hub length	1.77 in
Hardness of tread (D)	85 Shore D

DURATECH HEAT

BOG080x35-Ø8 HL45,5 (casquillo zinc)

EAN 4031582416459



BETTER MOBILITY. BETTER LIFE.

Product Drawings

