

ZETA

4681UAP200P63 XL

EAN 4031582399936



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ○ ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Zeta
Tip	Okreni Tocak sa usmerena kocnica
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	500 kg
Nosivost na 6 km/h	400 kg
Statički Nosivost	1000 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	85 °C
Sveukupna visina	240 mm
Ukupna težina	4,005 kg

TOCAK

Materijal za telo	poliamid
materijal omotaca	Poliuretan, liveno
Nošenje	precizini kuglicni lezaj
osovina	Završena sa navrtkom
stitnici omotaca	Sa threadguard
Prečnik	200 mm
Širina omotac	50 mm
Teškoća gazećeg omotac (A)	92 Šor A

KUCISTE

Materijal	Čelični list, veoma težak
oblik viljusa	siroko, Ojacano
okretni lezaj	Dve trke za loptu, Ojacano ili nerđajući
ofset	55 mm
Otpor okretanju	230 mm

PRILAGOĐAVANJE

Tip uklapanja	Pravougaona ploča
Dužina ploče	137 mm
Širina ploče	105 mm
Dužina otvora ploče (maksimalna)	105 mm
Širina otvora ploče (Minimalno)	75 mm
Širina otvora ploče (maksimalna)	80 mm
Prečnik otvora ploče	11 mm

ZETA

4681UAP200P63 XL

EAN 4031582399936



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

