

PRODUCT INFORMATION

DURATECH HEAT

WOO080x31 Ø12 TFR

EAN 4031582393842



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Duratech heat
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	200 kg
Electric Conductive	No
Stainless	No
Load capacity Static	400 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	180 °C
Overall weight	0.08 kg



BETTER MOBILITY. BETTER LIFE.

WHEEL

Body material	Thermoplastic synthetics, heat resistant
Tread Material Mix	Identical with wheel body
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	80 mm
Tread width	31 mm
Axle Hole Diameter	12 mm
Hub Length	40 mm
Hardness of tread (D)	75 Shore D

DURATECH HEAT

WOO080x31 Ø12 TFR

EAN 4031582393842



BETTER MOBILITY. BETTER LIFE.

Product Drawings

