

# AGILA

2470UAK050P40

EAN 4031582301090  
Order number 00004996



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                           |
|-----------------------------|---------------------------|
| Product name                | Agila                     |
| Housing type                | Swivel castor             |
| Standard                    | EN12530 - Devices Castors |
| Load capacity at 3 km/h     | 50 kg                     |
| Load capacity Static        | 100 kg                    |
| Temperature range (Minimum) | -25 °C                    |
| Temperature range (Maximum) | 80 °C                     |
| Overall height              | 69 mm                     |
| Overall width               | 43 mm                     |
| Overall weight              | 0.221 kg                  |

## WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Polyamide              |
| Tread material        | Polyurethane, injected |
| Bearing               | Cone ball bearing      |
| Wheel color           | Slate grey (RAL7015)   |
| Threadguards          | With threadguard       |
| Diameter              | 50 mm                  |
| Tread width           | 20 mm                  |
| Body width            | 20 mm                  |
| Hardness of tread (A) | 92 Shore A             |
| Hardness of tread (D) | 42 Shore D             |

## HOUSING

|                     |                     |
|---------------------|---------------------|
| Material fork       | Steel sheet, medium |
| Fork shape          | Broad               |
| Swivel bearing      | Two ball races      |
| Colour              | Blue passivated     |
| Offset              | 24 mm               |
| Swivel radius       | 49 mm               |
| Swivel interference | 98 mm               |
| Dome diameter       | 41 mm               |

## FITTING

|                             |              |
|-----------------------------|--------------|
| Fitting type                | Square plate |
| Plate length                | 60 mm        |
| Plate width                 | 60 mm        |
| Plate hole length (Minimum) | 38 mm        |
| Plate hole length (Maximum) | 48 mm        |
| Plate hole width (Minimum)  | 38 mm        |
| Plate hole width (Maximum)  | 48 mm        |
| Plate hole diameter         | 6.3 mm       |

# AGILA

2470UAK050P40

EAN 4031582301090  
Order number 00004996



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

