


NOVATECH

ETX085X85-Ø20 HL95-F

EAN 4031582369649



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja ● ● ● ○ ○

Buka u pokretu ● ● ● ○ ○

Ishrana ● ● ● ● ○

otpornost na rdju ● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda Novatech

Tip kućišta Tocak

Nosivost na 3 km/h 800 kg

Statički Nosivost 1600 kg

Temperaturni opseg (Minimalno) -20 °C

Opseg temperature (maksimalni) 60 °C

TOCAK

Materijal za telo Čelik, gvožđe

materijal omotaca Poliuretana, liveno

Nošenje precizini kuglicni lezaj, zapečaceno

stitnici omotaca Sa threadguard

Prečnik 85 mm

Širina omotac 85 mm

dimenzija rupa osovina 20 mm

dužina glavcine 95 mm

Teškoća gazećeg omotac (A) 92 Šor A

Tip zaptivke F

Pogodno za jungheinrich

TEHNIČKI CRTEŽI

