


NOVATECH

ETX085X85-Ø20 HL95-F

EAN 4031582369649



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	Čelik, gvožđe
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj, zapevaceno
stitnici omotaca	Sa threadguard
Prečnik	85 mm
Širina omotac	85 mm
dimenzija rupa osovina	20 mm
duzina glavčine	95 mm
Teškoća gazećeg omotac (A)	92 Šor A
Tip zaptivke	F
Pogodno za	jungheinrich

PERFORMANSE

Performanse kotrljanja ●●●○○

Buka u pokretu ●●●○○

Ishrana ●●●●○

otpornost na rdju ●●●○○

OSNOVNI ATRIBUTI

Naziv proizvoda Novatech

Tip Tocak

Nosivost na 3 km/h 800 kg

Statički Nosivost 1600 kg

Temperaturni opseg (Minimalno) -20 °C

Opseg temperature (maksimalni) 60 °C

NOVATECH

ETX085X85-Ø20 HL95-F

EAN 4031582369649



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

