PRODUCT INFORMATION

DURATECH

RK.TOP080x70-Ø47x14

EAN 4031582443103

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Undefined
Tread material	Polypropylene, soft
Diameter	3.15 in
Tread width	2.76 in
Ball bearing diameter	1.85 in
Ball bearing width	0.55 in

PERFORMANCE

Roll Performance	●●●●●
Movement noise	●●●○○
Attrition	●●●●●
Corrosion resistance	●●●○○

CORE ATTRIBUTES

Product name	Duratech
Type	Wheel
Load capacity at 1.8 mph	1433 lb
Electric conductive	no
Stainless	no
Load capacity Static	2866.01 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall weight	0.55 lb

© Copyright 2026 TENTE International GmbH

DURATECH

RK.TOP080x70-Ø47x14

EAN 4031582443103

BETTER MOBILITY. BETTER LIFE.

Product Drawings



