

LINEA CLINIC LOAD

5984UAP150R36-32S30 D 9002

EAN 4031582382518
Order number 00038181



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ● ● |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ● ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|---|
| Product name | Linea clinic load |
| Housing type | Swivel castor with central, total or directional lock |
| Standard | EN12530 - Devices Castors |
| Load capacity at 3 km/h | 200 kg |
| Load capacity Static | 400 kg |
| Temperature range (Minimum) | -10 °C |
| Temperature range (Maximum) | 40 °C |
| Overall height | 155 mm |
| Overall width | 71 mm |
| Overall weight | 1.624 kg |

WHEEL

| | |
|-----------------------|------------------------|
| Body material | Polyamide |
| Tread material | Polyurethane, injected |
| Bearing | Precision ball bearing |
| Wheel color | Slate grey (RAL7015) |
| Threadguards | With threadguard |
| Diameter | 150 mm |
| Tread width | 15 mm |
| Body width | 15 mm |
| Hardness of tread (A) | 92 Shore A |
| Hardness of tread (D) | 42 Shore D |

HOUSING

| | |
|---------------------|---|
| Material fork | Polyamide |
| Fork shape | Twin wheel housing |
| Swivel bearing | Two ball races, reinforced or stainless |
| Colour | Grey white (RAL9002) |
| Offset | 47.5 mm |
| Swivel radius | 122.5 mm |
| Swivel interference | 245 mm |
| Dome diameter | 46 mm |

FITTING

| | |
|------------------------------|--|
| Fitting type | Stem with cam hole for profile bars, short version |
| Bolt diameter | 32 mm |
| Bolt length | 51 mm |
| Bolt thread position | 7 mm |
| Bolt mounting holes quantity | 2 |

