

# AGILA

267FPJO5X1.25P30-13

EAN 4031582435405



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance ● ● ● ○ ○

Movement noise ● ● ○ ○ ○

Attrition ● ● ● ● ○

## CORE ATTRIBUTES

|                         |                                              |
|-------------------------|----------------------------------------------|
| Product name            | Agila                                        |
| Housing type            | Castor with butterfly wheel brake            |
| Standard                | Institute of Casters and Wheel Manufacturers |
| Load capacity at 3 km/h | 125 kg                                       |
| Load capacity Static    | 250 kg                                       |
| Overall height          | 155 mm                                       |

## WHEEL

|                       |                      |
|-----------------------|----------------------|
| Body material         | Polypropylene        |
| Tread material        | Thermoplastic rubber |
| Bearing               | Plain bearing        |
| Threadguards          | Without threadguard  |
| Diameter              | 127 mm               |
| Tread width           | 31.75 mm             |
| Axle hole diameter    | 10 mm                |
| Hardness of tread (A) | 77 Shore A           |

## HOUSING

|                     |                     |
|---------------------|---------------------|
| Material fork       | Steel sheet, medium |
| Fork shape          | Broad, reinforced   |
| Swivel bearing      | Two ball races      |
| Offset              | 37 mm               |
| Swivel radius       | 100.5 mm            |
| Swivel interference | 201 mm              |

## FITTING

|                    |                                                            |
|--------------------|------------------------------------------------------------|
| Fitting type       | Bolt hole                                                  |
| Bolt hole diameter | 13 mm                                                      |
| Hint               | Castors can be mounted with standard screws of any length. |