

ZETA

4680IFP160P63

EAN 4031582365955
Order number 00837654



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Zeta
Housing type	Swivel castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	350 kg
Load capacity at 6 km/h	280 kg
Load capacity Static	700 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	85 °C
Overall height	200 mm
Overall width	96 mm
Overall weight	3.345 kg

WHEEL

Body material	Aluminium
Tread material	Elastic tire, non-marking, vulcanized
Bearing	Precision ball bearing
Axle	Screwed with nut
Wheel color	Grey / non- marking
Threadguards	Without threadguard
Diameter	160 mm
Tread width	50 mm
Body width	50 mm
Hardness of tread (A)	67 Shore A

HOUSING

Material	Steel sheet, very heavy
Fork shape	Broad, reinforced
Swivel bearing	Two ball races, reinforced or stainless
Colour	Blue passivated
Offset	55 mm
Swivel radius	135 mm
Swivel interference	270 mm
Dome diameter	96 mm

FITTING

Fitting type	Rectangular plate
Plate length	137 mm
Plate width	105 mm
Plate hole length (Minimum)	75 mm
Plate hole length (Maximum)	80 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	105 mm
Plate hole diameter	11 mm

ZETA

4680IFP160P63

EAN 4031582365955
Order number 00837654



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

