

# DURATECH PLUS

MMP050X26-Ø15

EAN 4031582399370  
Broj porudžbine 00860912



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## TOCAK

|                            |                           |
|----------------------------|---------------------------|
| Materijal za telo          | poliamid, super težak     |
| materijal omotaca          | Dupli prirubnici sa trake |
| Nošenje                    | precizini kuglicni lezaj  |
| stitnici omotaca           | Bez stražara              |
| Prečnik                    | 50 mm                     |
| Širina omotac              | 26 mm                     |
| dimenzija rupa osovina     | 15 mm                     |
| dužina glavnice            | 32 mm                     |
| Teškoća gazećeg omotac (D) | 75 Šor D                  |

## PERFORMANSE

|                        |           |
|------------------------|-----------|
| Performanse kotrljanja | ● ● ● ● ● |
| Buka u pokretu         | ● ● ● ○ ○ |
| Ishrana                | ● ● ● ● ● |
| otpornost na rdju      | ● ● ● ○ ○ |

## OSNOVNI ATRIBUTI

|                                |                                  |
|--------------------------------|----------------------------------|
| Naziv proizvoda                | Duratech plus                    |
| Tip kućišta                    | Tocak                            |
| Standard                       | EN12533 - Tockoviza teske terete |
| Nosivost na 4 km/h             | 240 kg                           |
| Nosivost na 6 km/h             | 200 kg                           |
| Statički Nosivost              | 480 kg                           |
| Temperaturni opseg (Minimalno) | -40 °C                           |
| Opseg temperature (maksimalni) | 80 °C                            |

# DURATECH PLUS

MMP050X26-Ø15

EAN 4031582399370  
Broj porudžbine 00860912



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

