

DURATECH PLUS

MMP050X26-Ø15

EAN 4031582399370
Broj porudžbine 00860912

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	poliamid, super težak
materijal omotaca	Dupli prirubnici sa trake
Nošenje	precizini kuglicni lezaj
stitnici omotaca	Bez stražara
Prečnik	50 mm
Širina omotac	26 mm
dimenzija rupa osovina	15 mm
dužina glavčine	32 mm
Teškoća gazećeg omotac (D)	75 Šor D

PERFORMANSE

Performanse kotrljanja	● ● ● ● ●
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Duratech plus
Tip	Tocak
Standard	EN12533 - Tockoviza teske terete
Nosivost na 4 km/h	240 kg
Nosivost na 6 km/h	200 kg
Statički Nosivost	480 kg
Temperaturni opseg (Minimalno)	-40 °C
Opseg temperature (maksimalni)	80 °C

DURATECH PLUS

MMP050X26-Ø15

EAN 4031582399370
Broj porudžbine 00860912



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

