

SUPRATECH

PJR100X32-Ø12 HL44,4 BLUE

EAN 4031582355185



BETTER MOBILITY. BETTER LIFE.

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|---------------------------|
| Product name | Supratech |
| Type | Wheel |
| Standard | EN12530 - Devices Castors |
| Load capacity at 3 km/h | 80 kg |
| Load capacity Static | 160 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 60 °C |
| Overall weight | 0.136 kg |

WHEEL

| | |
|--------------------|----------------------|
| Body material | Polypropylene |
| Tread material | Thermoplastic rubber |
| Bearing | Roller bearing |
| Threadguards | Without threadguard |
| Diameter | 100 mm |
| Tread width | 32 mm |
| Axle hole diameter | 12 mm |
| Hub length | 44.4 mm |

SUPRATECH

PJR100X32-Ø12 HL44,4 BLUE

EAN 4031582355185

TECHNICAL DRAWINGS

