

ALPHA

3478DIJ200P63

EAN 4031582306255
Order number 00030041



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ● ● ●
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Alpha
Type	Fixed castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	205 kg
Load capacity Static	410 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	240 mm
Overall weight	2.972 kg

WHEEL

Body material	Sheet Steel
Tread material	Solid rubber, non-marking
Bearing	Roller bearing
Axle	Screwed with nut
Threadguards	With threadguard
Diameter	200 mm
Tread width	50 mm
Hardness of tread (A)	80 Shore A

HOUSING

Material fork	Steel sheet, heavy
Fork shape	Broad

FITTING

Fitting type	Medium rectangular plate
Plate length	137 mm
Plate width	115 mm
Plate hole length (Maximum)	105 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	80 mm
Plate hole diameter	11 mm

ALPHA

3478DIJ200P63

EAN 4031582306255
Order number 00030041



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

