

LUMINA

A525POI050L51-8 BLANCA

EAN 4031582439236



BETTER MOBILITY. BETTER LIFE.

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Lumina
Housing type	Swivel castor with wheel brake
Standard	EN12528 - Furniture Castors
Load capacity at 1.8 mph	88.18 lb
Load capacity Static	176.37 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall height	2.2 in
Overall width	2.13 in
Overall weight	0.12 lb

WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	1.97 in
Tread width	0.28 in
Hardness of tread (D)	65 Shore D

HOUSING

Material	Polypropylene
Fork shape	Twin wheel housing, closed, with dome
Swivel bearing	Stem, swiveling
Swivel radius	2.44 in
Swivel interference	4.88 in

FITTING

Fitting type	Blind hole for B10 fitting
Bolt hole diameter	0.31 in

PRODUCT INFORMATION

LUMINA

A525POI050L51-8 BLANCA

EAN 4031582439236



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

