

KAPPA LOAD

9650TOO125P63

EAN 4031582348743



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja	● ● ● ● ●
Buka u pokretu	● ○ ○ ○ ○
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Kappa load
Tip	Okretanje Tocak
Standard	EN12533 - Tockovi za teske terete
Nosivost na 4 km/h	840 kg
Nosivost na 6 km/h	700 kg
Električni provod	no
nerdjajuci	no
Statički Nosivost	1680 kg
Temperaturni opseg (Minimalno)	-40 °C
Opseg temperature (maksimalni)	80 °C
Sveukupna visina	170 mm
Ukupna težina	3 kg

KUCISTE

Materijal kućišta	Gvožđe ili gvožđe kovano, teško
oblik viljusk	siroko, Ojacano
okretni lezaj	kotrljajući lezaj sa kuglom dubokog rasta
ofset	48 mm
okretni radijus	110.5 mm
Otpor okretanju	221 mm
Lubrication nipple	1

TOCAK

Materijal za telo	poliamid težak
materijal omotaca	Identično sa telom Tocak
Nošenje	klizni lezaj
osovina	Završena sa navrtkom
stitnici omotaca	Bez stražara
Prečnik	125 mm
Širina omotac	50 mm
Teškoća gazećeg omotac (D)	75 Šor D

PRILAGOĐAVANJE

Tip uklapanja	Pravougaona ploča
Dužina ploče	135 mm
Širina ploče	110 mm
Dužina otvora ploče (maksimalna)	105 mm
Širina otvora ploče (Minimalno)	75 mm
Širina otvora ploče (maksimalna)	80 mm
Prečnik otvora ploče	11 mm

KAPPA LOAD

9650TOO125P63

EAN 4031582348743

Broj porudžbine 00838705
Product Drawings



BETTER MOBILITY. BETTER LIFE.

