PRODUCT INFORMATION

PURETECH

PVO160x40-Ø20 HL58

EAN 4031582442366

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polypropylene
Tread Material Mix	Solid rubber, black
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	160 mm
Tread width	40 mm
Axle Hole Diameter	20 mm
Hub Length	58 mm
Hardness of tread (A)	85 Shore A

PERFORMANCE

Roll Performance	●●○○○
Movement Noise	●●●○○
Attrition	●●○○○
Corrosion Resistance	●●●○○

CORE ATTRIBUTES

Product Name	Puretech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	135 kg
Electric Conductive	No
Stainless	No
Load capacity Static	270 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.7 kg

© Copyright 2026 TENTE International GmbH


PURETECH

PVO160x40-Ø20 HL58

EAN 4031582442366

BETTER MOBILITY. BETTER LIFE.

Product Drawings



© Copyright 2026 TENTE International GmbH