

PRODUCT INFORMATION

BASETECH

POR080x34-Ø12 RAL9011

EAN 4031582320763



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

| | |
|-----------------------|---------------------------|
| Body material | Polypropylene |
| Tread material | Identical with wheel body |
| Bearing | Roller bearing |
| Threadguards | Without threadguard |
| Diameter | 3.15 in |
| Tread width | 1.34 in |
| Axle hole diameter | 0.47 in |
| Hub length | 1.75 in |
| Hardness of tread (D) | 65 Shore D |

PERFORMANCE

| | |
|----------------------|-------------|
| Roll Performance | ● ● ● ● ○ ○ |
| Movement noise | ● ● ● ● ○ ○ |
| Attrition | ● ● ● ● ● ● |
| Corrosion resistance | ● ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Basetech |
| Type | Wheel |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 2.5 mph | 275.58 lb |
| Electric conductive | no |
| Stainless | no |
| Load capacity Static | 551.16 lb |
| Temperature range (Minimum) | -4 °F |
| Temperature range (Maximum) | 140 °F |
| Overall weight | 0.22 lb |

BASETECH

POR080x34-Ø12 RAL9011

EAN 4031582320763

Order number 00030950
Product Drawings



BETTER MOBILITY. BETTER LIFE.

