

AGILA TWIN

2975UAH050P30-11

EAN 4031582413755



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Agila twin
Housing type	Swivel castor with wheel brake
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	70 kg
Load capacity Static	140 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall height	69 mm
Overall width	53 mm
Overall weight	0.29 kg

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Plain bearing
Threadguards	With threadguard
Diameter	50 mm
Tread width	19 mm
Hardness of tread (D)	40 Shore D

HOUSING

Material fork	Steel sheet, medium
Fork shape	Twin wheel housing
Swivel bearing	Two ball races
Offset	25 mm
Swivel radius	77.5 mm
Swivel interference	155 mm

FITTING

Fitting type	Bolt hole
Bolt hole diameter	11 mm

AGILA TWIN

2975UAH050P30-11

EAN 4031582413755



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

