

ALPHA STAINLESS

8478UOD200P63

EAN 4031582333121
Order number 00065024



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Alpha stainless
Type	Fixed castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	500 kg
Stainless	✓
Load capacity Static	1000 kg
Temperature range (Minimum)	-25 °C
Temperature range (Maximum)	80 °C
Overall height	240 mm
Overall width	115 mm
Overall weight	1.985 kg

WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Roller bearing, stainless
Axle	Screwed with nut
Wheel color	Natural white
Diameter	200 mm
Tread width	50 mm
Body width	50 mm
Hardness of tread (D)	75 Shore D

HOUSING

Material fork	Stainless steel, heavy
Fork shape	Broad
Colour	Stainless steel

FITTING

Fitting type	Medium rectangular plate
Plate length	140 mm
Plate width	115 mm
Plate hole length (Minimum)	75 mm
Plate hole length (Maximum)	80 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	105 mm
Plate hole diameter	11 mm

ALPHA STAINLESS

8478UOD200P63

EAN 4031582333121
Order number 00065024



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

