

ALPHA STAINLESS

8470UAD100P30-13 NATURAL/3004

EAN 4031582312393
Order number 00062162



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ● ● |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Alpha stainless |
| Housing type | Swivel castor |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 4 km/h | 150 kg |
| Load capacity Static | 300 kg |
| Temperature range (Minimum) | -25 °C |
| Temperature range (Maximum) | 80 °C |
| Overall height | 128 mm |
| Overall width | 75 mm |
| Overall weight | 0.69 kg |

WHEEL

| | |
|-----------------------|---------------------------|
| Body material | Polyamide |
| Tread material | Polyurethane, injected |
| Bearing | Roller bearing, stainless |
| Axle | Screwed with nut |
| Wheel color | Natural white |
| Diameter | 100 mm |
| Tread width | 32 mm |
| Body width | 32 mm |
| Hardness of tread (A) | 92 Shore A |
| Hardness of tread (D) | 42 Shore D |

HOUSING

| | |
|---------------------|------------------------|
| Material | Stainless steel, heavy |
| Fork shape | Broad |
| Swivel bearing | Two ball races |
| Colour | Stainless steel |
| Offset | 41 mm |
| Swivel radius | 91 mm |
| Swivel interference | 182 mm |
| Dome diameter | 75 mm |
| Stainless | ✓ |

FITTING

| | |
|--------------------|-----------|
| Fitting type | Bolt hole |
| Bolt hole diameter | 13 mm |

ALPHA STAINLESS

8470UAD100P30-13 NATURAL/3004

EAN 4031582312393
Order number 00062162



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

