

# PURETECH

UVH 080X35 HL46

EAN 4031582323627  
Order number 00002549



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polyamide
Tread material	Solid rubber, black
Bearing	Plain bearing
Wheel color	Graphite black (RAL9011)
Threadguards	With threadguard
Diameter	80 mm
Tread width	35 mm
Axle hole diameter	8.3 mm
Hub length	46 mm
Body width	35 mm
Hardness of tread (A)	90 Shore A
Hardness of tread (D)	39 Shore D

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Puretech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	100 kg
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	80 °C
Overall weight	0.218 kg

# PURETECH

UVH 080X35 HL46

EAN 4031582323627  
Order number 00002549



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

