

# DELTA TWIN

9948ITP125P63 SOFT CV

EAN 4031582365894  
Order number 00837761



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Delta twin
Housing type	Fixed castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	750 kg
Load capacity at 6 km/h	600 kg
Load capacity Static	1500 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall height	178 mm
Overall width	157 mm
Overall weight	3.857 kg

## WHEEL

Body material	Aluminium
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Wheel color	Traffic grey A (RAL7042)
Threadguards	Without threadguard
Diameter	125 mm
Tread width	50 mm
Body width	50 mm
Hardness of tread (A)	80 Shore A

## HOUSING

Material	Iron forged, heavy
Fork shape	Twin wheel housing
Colour	Transparent coating
Dome diameter	136 mm

## FITTING

Fitting type	Rectangular plate
Plate length	137 mm
Plate width	137 mm
Plate hole length (Minimum)	75 mm
Plate hole length (Maximum)	80 mm
Plate hole width (Minimum)	105 mm
Plate hole width (Maximum)	105 mm
Plate hole diameter	11 mm

# DELTA TWIN

9948ITP125P63 SOFT CV

EAN 4031582365894  
Order number 00837761



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

