PRODUCT INFORMATION

PURETECH AIR

DPR200x50-Ø20 2PR black

EAN 4031582371024

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Tread hardness	soft
Body material	Sheet Steel
Tread material	Pneumatic tire, line profile
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	7.87 in
Tread width	1.97 in
Axle hole diameter	0.79 in
Hub length	2.28 in
Hardness of tread (A)	55 Shore A

PERFORMANCE

Roll Performance	● ○ ○ ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Puretech air
Type	Wheel
Load capacity at 1.8 mph	165.35 lb
Electric conductive	no
Stainless	no
Load capacity Static	330.69 lb
Overall weight	1.76 lb

© Copyright 2026 TENTE International GmbH


PURETECH AIR

DPR200x50-Ø20 2PR black

EAN 4031582371024

BETTER MOBILITY. BETTER LIFE.

Product Drawings



© Copyright 2026 TENTE International GmbH